

Help Reduce Contamination With The EcoCare™ Complete Foot and Hand Sanitation Program



Whave put ourselves into your shoes. We know that the safety and quality of the foods and beverages you produce are big concerns. Therefore we developed the EcoCare Complete Doorway Sanitation Program.

We also know that you need a comprehensive protection program to stop the spread of contaminants from workers' hands to the foods and beverages they help to produce. Hand washing and sanitizing can significantly reduce that threat. Thus we developed the EcoCare Hand Sanitation Program.

Used together, these integrated programs (soaps, sanitizers and dispensing systems) help safeguard the integrity of your good manufacturing practices.



Doorway Systems



EcoCare Model ADS
Automatic Doorway Spray
Infrared sensor triggers spray.

EcoCare Model TDS
Timed Doorway Spray
Ten to fifteen minute timer
triggers spray.

EcoCare Model ADF
Automatic Doorway Foam
Infrared sensor triggers foam.

EcoCare Model TDF
Timed Doorway Foam
Ten to fifteen minute timer
triggers foam.

Products dispensed:
EcoCare 650 (Quat)
EcoCare 660
(Peroxyacetic acid)

Products dispensed:
EcoCare 650 (Quat)
EcoCare 660
(Peroxyacetic acid)

Products dispensed:
EcoCare 650 (Quat)
EcoCare 660 with
EcoCare 600FA
(foaming agent)

Products dispensed:
EcoCare 650 (Quat)
EcoCare 660 with
EcoCare 600FA
(foaming agent)

Central Distribution Systems



EcoCare Model NTS
No Touch Solenoid

Products dispensed:
EcoCare 250, 270 & 360

Local Distribution Systems



EcoCare NTP & NTR-2
No Touch Pump w/2-liter reservoir

Products dispensed:
EcoCare 250, 270, 350, & 360



EcoCare NTP & NTR-8
No Touch Pump w/8-liter reservoir

Products dispensed:
EcoCare 250, 270, 350, & 360

Manual Dispensing Systems



EcoCare Model NTFS
No Touch, Free Standing
Foot Operated

Products dispensed:
EcoCare 250, 270, 350, & 360



EcoCare Model NTW
No Touch, Wall Mounted,
Foot Operated

Products dispensed:
EcoCare 250, 270, 350, & 360



EcoCare Model NTB
No Touch, Battery
Operated

Products dispensed:
EcoCare 250, 270 & 450L



EcoCare Model LPB
Large Push Button, 3-liter

Products dispensed:
EcoCare 250, & 270



EcoCare Model HAF
Hand Activated Foam

Products dispensed:
EcoCare 370



EcoCare Model GT
Hand Activated, Grit

Products dispensed:
EcoCare 410M (Pumice)



EcoCare Model PB
Push Button, Wall Mounted

Products dispensed:
EcoCare 250, 270 & 450L



EcoCare Model FPB
Foam Push Button

Products dispensed:
EcoCare 360 & 275



EcoCare Model HC
Hand Crank

Products dispensed:
EcoCare 250



EcoCare Model MD
Manual Dispenser

Products dispensed:
EcoCare 160, 195, 250 & 360