



MODEL 4450 DROP STATION BOOSTED PRESSURE RINSE

Product Description

The Ecolab Model 4450 Drop Station is a wall mounted, boosted-pressure rinse station, ready for owner's hook-up of boosted pressure water and air. It provides controlled, convenient point-of-use rinse water to clean food and beverage product contact and facility surfaces.

Benefits

- Compact
- Durable
- Easy to Use
- Cost Efficient
- Convenient
- Controls Water

Standard Features

- SS construction
- Mounting brackets
- Shut-off ball valve
- SS flow restrictor
- Quick connect hose fitting
- SS heavy duty hose hanger
- Rinse nozzle

Applications

The 4450 boosted-pressure rinse station is a point-of-use unit for equipment and facility cleaning using 100-400 psi incoming water. This provides convenient and efficient rinsing for facility and product contact surfaces in food or beverage processing facilities.

