

DISHMACHINE PORTFOLIO

SUPERIOR PERFORMANCE ■ 24/7 SERVICE ■ BETTER FINANCIAL OPTION

SINGLE DOOR MACHINES



(Available in Vapor Vent Option)



(Available in Vapor Vent Option)

	APEX™ TSC SINGLE RACK	APEX™ HT	XL-HT	ES-2000 ■ XL-2000	ES-2000HT**	
Racks/Hour (NSF Rating)	46	57	57	40	55	
Gallons/Rack (NSF Rating)	1.02	0.83	0.83	1.02	1.25	
Sanitizing Method: Chemical vs. Temperature						
Products	Apex™	Apex™	Solid Power™	Liquid	Solid Power™	Liquid
Wash Chamber Height	17"	17"	17"	17"	17"	17"
Dimensions*	69 ³ / ₄ "x25 ¹ / ₄ "x25 ¹ / ₄ "	70 ³ / ₄ "x25 ¹ / ₄ "x25 ¹ / ₄ "	70 ³ / ₄ "x25 ¹ / ₄ "x25 ¹ / ₄ "	64 ¹ / ₄ "x25 ¹ / ₄ "x25 ¹ / ₄ "	67"x25 ¹ / ₄ "x25 ¹ / ₄ "	



Improve Warewashing Results

Booster Heater
Ensures proper water temperatures for clean, sanitized ware

POU Softener
Reduces spotting, streaking and filming on glassware

DOUBLE DOOR MACHINES



	APEX™ TSC DOUBLE RACK	ES-4000 ■ XL-4000	
Racks/Hour (NSF Rating)	78	78	
Gallons/Rack (NSF Rating)	1.17	1.17	
Sanitizing Method: Chemical vs. Temperature			
Products	Apex™	Liquid	Solid Power™
Wash Chamber Height	17"	17"	17"
Dimensions*	69 ³ / ₄ "x44 ¹ / ₈ "x25 ⁷ / ₈ "	64 ¹ / ₄ "x44 ¹ / ₈ "x25 ⁷ / ₈ "	

* Distance between the tables
** Available in US Only



DISHMACHINE PORTFOLIO

SUPERIOR PERFORMANCE ■ 24/7 SERVICE ■ BETTER FINANCIAL OPTION

CONVEYOR MACHINES



	APEX™ CONVEYOR 44	APEX™ CONVEYOR 66	EC-44/EC-44HH	EC-66/EC-66HH
Racks/Hour (NSF Rating)	200	200	244	244
Gallons/Rack (NSF Rating)	0.57	0.57	0.91	0.91
Sanitizing Method: Chemical vs. Temperature				
Products	Apex™	Apex™	Apex™/Solid Power™	Apex™/Solid Power™
Wash Chamber Height	17 1/2"	17 1/2"	18"/25" (HH)	18"/25" (HH)
Dimensions*	71 1/2"x44 1/2"x35"	71 1/2"x66 1/2"x35"	68"x43 3/4"x27" 75"x43 3/4"x27" (HH)	68"x65 3/4"x32 3/8" 75"x65 3/4"x32 3/8" (HH)

UNDERCOUNTER/GLASSWARE MACHINES



	DF ROTARY	OMEGA 5E	U-HT†	U-LT††
Racks/Hour (NSF Rating)	1000 glasses/hr	31	30	21
Gallons/Rack (NSF Rating)	2.8 gal/min	1.16	0.78	1.6
Sanitizing Method: Chemical vs. Temperature				
Products	Liquid	Liquid	Liquid	Liquid
Wash Chamber Height	10"	11 1/2"	14 3/4"	14 3/4"
Dimensions*	39"x25"x27"	38"x24 1/4"x25 1/4"	33 3/4"x24"x25"	33 3/4"x24"x25"

* Distance between the tables

† Canada 501-HT
†† Canada 501-LT