



POWERFUL DEGREASING. MADE SAFER*.

Greaselift

- ▲ Penetrates grease and lifts it from surfaces
- ▲ Requires no gloves or goggles
- ▲ Foaming action for vertical clinging
- ▲ Aluminum safe
- ▲ Biodegradeable

Powerful degreaser
requires no gloves or goggles
to clean ovens, grills, stove
hoods and vents.



* When compared with caustic degreasers.
Greaselift is noncorrosive and less irritating.

ECOLAB®

GREASELIFT FEATURES A UNIQUE TECHNOLOGY THAT ACTUALLY PENETRATES TOUGH, BAKED ON GREASE AND LIFTS IT AWAY FROM THE SURFACE.

MANUAL OVEN CLEANING

It is a powerful degreaser, even though it does not require gloves or goggles to use. It is available in ready-to-use bottles or as a concentrate that can be dispensed into a reusable spray bottle or hand sprayer, which helps significantly reduce packaging waste. Greaselift is biodegradable, has no noxious odors, and won't damage aluminum surfaces.



before



applied with pump-up sprayer







after

DIRECTIONS

1. Spray Greaselift onto warm (120°F/49°C) surface with carbonized grease. Cover soiled areas completely with foam.
2. Allow Greaselift to penetrate grease soils for 1-5 minutes. Do not let product dry on surface.
3. Wipe off dissolved and loosened grease with a nonabrasive pad or a damp towel.
4. Rinse surface with clear water.

NOTE: Caution should be used when cleaning hot surfaces.

	PRODUCT	ITEM #	PACK SIZE
	Greaselift	1110168	1 - 2 L bag
	Greaselift RTU	1110169	6 - 32 fl oz btl
	Greaselift Spray Bottle	92211239	3 - 32 fl oz
	Greaselift Pump Up Sprayer	92211261	1 - 32 fl oz



For maximum ease of use and safety when cleaning ovens, use Ecolab's Hi-Temp Tools with new Greaselift.