



# VENTLESS WAREWASHING SYSTEM

## EHT-V Dishmachine

Best results with lowest total cost. Less reliance on the operator through integration of machine, chemical, and automated machine procedures.


- ▲ Integrated heat recovery system captures water vapor (steam) to enable ventless operation
- ▲ SMARTCYCLE™ provides ware specific cycles to enable best results to meet your operational needs
- ▲ Automated Procedures reduce reliance on operator for improved procedure compliance
- ▲ High Pressure Rinse Technology reduce Water/Energy up to 50%



# Ecolab Dishmachine Rental Program

Technology that simplifies, delivering consistently clean wares backed by service you can trust.

All dimensions in inches



## SPECIFICATIONS

OPERATING CAPACITY		
Racks per Hour	48	
OPERATING CYCLE NORMAL		
Wash Time	45	
Dwell Time	18	
Rinse Time	7	
Total Cycle Time	70	
OPERATING TEMPERATURES		
Wash (minimum)	155°F	
Sanitizing Rinse (minimum)	180°F	
WATER CONSUMPTION		
Gallons per Rack	0.47	
Gallons per Hour	27.6	
WASH CHAMBER		
Height	18.25"	
WEIGHT		
Machine Weight	480 lb	
UTILITY REQUIREMENTS, ELECTRICAL		
	Power Connection	
	Single	Multiple*
Voltage/Frequency/Phase: 240V/60Hz/1 Ph		
Total Amperage	81.5 A	29.2/52.3 A
Minimum Electrical Circuit	90 A	30/60 A
Voltage/Frequency/Phase: 240V/60Hz/3 Ph		
Total Amperage	49.8 A	16.8/33 A
Minimum Electrical Circuit	60 A	20/40 A
Voltage/Frequency/Phase: 208V/60Hz/3 Ph		
Total Amperage	56.4 A	19.4/37 A
Minimum Electrical Circuit	60 A	20/40 A
Voltage/Frequency/Phase: 208V/60Hz/1 Ph		
Total Amperage	93 A	33.6/59.4 A
Minimum Electrical Circuit	100 A	40/70 A
HOT WATER		
Waterline Size (minimum)	1/2" NPT	
Flow Pressure (required)	10-30 psi	
Incoming Temperature (minimum)	120°F	
COLD WATER		
Waterline Size (minimum)	1/2" NPT	
Flow Pressure (required)	10-30 psi	
HEAT TO SPACE		
Latent	8,560 btu	
Sensible	4,860 btu	
Total	13,420 btu	

\* Booster/Machine

## PRODUCTS FOR USE IN THE EHT-V MACHINE



**SMARTPOWER™**  
Dishmachine Detergent  
6101201 4-6.75 lb  
6101202 6-6.75 lb



**SMARTPOWER™**  
Rinse Additive Heavy Duty  
6101199 2-2.5 lb



**SMARTPOWER™**  
Dishmachine Detergent  
Heavy Duty  
6101200 4-6.75 lb



**SMARTPOWER™**  
Rinse Additive All Purpose  
6101203 2-2.5 lb



**SMARTPOWER™**  
Dishmachine Detergent  
Specialty  
6101308 4-6.75 lb



**Solid Power™ XL**  
Dishmachine Detergent  
6100185 4-9 lb  
6100183 2-9 lb



**SMARTPOWER™**  
Dishmachine Detergent  
Metal Safe  
6101307 4-6.75 lb



**Solid Brilliance**  
Rinse Additive  
6125395 2-2.5 lb



**LIME-A-WAY**  
6101131 4-1 gal

