

Foodservice success at every level



DELIGHTED GUESTS

- Shining wares and clean surfaces
- A visible commitment to clean and safety
- Great-tasting food & beverage, both on and off premises



PROTECTED REPUTATIONS

- Comprehensive, science-based solutions to help reduce risk
- Training and service to help ensure compliance
- Prioritized insights for clean and sanitized wares



OPTIMIZED OPERATIONS

- Training and expertise to drive consistency and simplicity
- Products and programs that increase labor efficiency
- Sustainable programs that reduce water, energy and waste

Expert service, personally delivered.

Around the world, around the clock, we're always nearby.
Nobody has more warewashing experts in the field than Ecolab.

THE ECOLAB DISH MACHINE RENTAL PROGRAM

The highest level of clean is backed by service you can trust.

- 24/7/365 support
- On-site training
- Regular preventive maintenance
- Business consultation
- Technical support
- A single point of contact
- Parts, labor and materials



Upgrade your warewashing operation with unmatched technology and service.

Visit www.ecolab.com/solutions/commercial-dishmachines or call **1 800 35 CLEAN** to learn more about the Ecolab Dishmachine Rental Program.



Dishmachine Portfolio

A DISH MACHINE FOR EVERY FOODSERVICE OPERATION

The highest level of clean at the lowest total cost.

1 SINGLE-DOOR MACHINES



EHT		
AVAILABLE IN VENTLESS OPTION: EHT-V		
High temp for fast drying. Automated procedures. Auto deliming. High-pressure rinse.		
55 Racks/Hour	0.47 Gallons/Rack	Temperature Sanitizing Method
Products: SMARTPOWER™ Solid Power™		
Wash Chamber Height: 18 1/4"		
Dimensions*: 74" x 25 1/4" x 25 1/4"		



XL-HT XL-HT HH		
High temp with onboard booster heater. Utilizes Energy Star® rating.		
58 Racks/Hour	0.79 Gallons/Rack	Temperature Sanitizing Method
Products: Solid Power™		
Wash Chamber Height: 17" 27" (HH)		
Dimensions*: 70 3/4" x 25 1/4" x 25 1/4" (HH) 81" x 25 1/4" x 25 1/4" (HH)		



SMARTPOWER™ TSC SINGLE RACK		
AVAILABLE IN VAPOR VENT OPTION		
The first all-solid, low-temp, Energy Star® warewashing system.		
40 Racks/Hour	1.02 Gallons/Rack	Chemical Sanitizing Method
Products: SMARTPOWER™		
Wash Chamber Height: 17"		
Dimensions*: 69 3/4" x 25 1/4" x 25 1/4"		



ES-2000		
Low temp, Energy Star® with self-cleaning internal sump. Clean water in every cycle.		
40 40 Racks/Hour	1.02 1.02 Gallons/Rack	Chemical Sanitizing Method
Products: Liquid Solid Power™		
Wash Chamber Height: 19"		
Dimensions*: 64 1/4" x 25 1/4" x 25 1/4"		



ES-2000HT**		
AVAILABLE IN VAPOR VENT OPTION: ES200HT VV		
High temp for fast drying with self-cleaning internal sump.		
55 Racks/Hour	1.25 Gallons/Rack	Temperature Sanitizing Method
Products: Liquid		
Wash Chamber Height: 17"		
Dimensions*: 67" x 25 1/4" x 25 1/4"		

2 DOUBLE-DOOR MACHINES



SMARTPOWER™ TSC DOUBLE RACK		
All-solid, low-temp warewashing system with integrated efficiency tracking.		
78 Racks/Hour	1.17 Gallons/Rack	Chemical Sanitizing Method
Products: SMARTPOWER™		
Wash Chamber Height: 17"		
Dimensions*: 69 3/4" x 44 1/8" x 25 7/8"		



ES-4000 XL-4000		
Low temp, Energy Star® with self-cleaning sump.		
78 78 Racks/Hour	1.17 1.17 Gallons/Rack	Chemical Sanitizing Method
Products: Liquid Solid Power™		
Wash Chamber Height: 19" 19"		
Dimensions*: 64 1/4" x 44 1/8" x 25 7/8"		

IMPROVE WAREWASHING RESULTS



BOOSTER HEATER
ensures proper water temperatures for clean, sanitized wares.



POU SOFTENER
reduces spotting, filming and streaking on glassware.



LEGEND:



Temperature
Sanitizing Method



Chemical
Sanitizing Method

* Distance between the tables
** Available in U.S. only
† Canada 501-HT
†† Canada 501-LT

Racks/Hour and Gallons/Rack = NSF Rating

3 CONVEYOR MACHINES



EC-44-LW EC-44HH-LW		
The high hood model boasts a 25" wash chamber (EC-44HH-LW) to fit larger wares. Energy Star conveyor.		
244 Racks/Hour	0.62 Gallons/Rack	Sanitizing Method
Products: SMARTPOWER™ Solid Power™		
Wash Chamber Height: 18" 25" (HH)		
Dimensions*: 68" x 43 3/4" x 27" 75" x 43 3/4" x 27" (HH)		



EC-66-LW EC-66HH-LW		
Built for heavy duty, the '66 features a 1hp prewash pump and robust electrical system.		
244 Racks/Hour	0.62 Gallons/Rack	Sanitizing Method
Products: SMARTPOWER™ Solid Power™		
Wash Chamber Height: 18" 25" (HH)		
Dimensions*: 68" x 65 3/4" x 32 3/8" 75" x 65 3/4" x 32 3/8" (HH)		

4 UNDERCOUNTER/ GLASSWARE MACHINES



E-UHT†		
High-temp, Energy Star® undercounter with fresh water recirculating design for one-pass results.		
27 Racks/Hour	0.76 Gallons/Rack	Temperature Sanitizing Method
Products: Liquid		
Wash Chamber Height: 14 3/4"		
Dimensions*: 34" x 24" x 25"		



E-ULT††		
Low-temp, Energy Star® undercounter. Easy to operate user interface. Interior LED lighting.		
25 Racks/Hour	0.84 Gallons/Rack	Chemical Sanitizing Method
Products: Liquid		
Wash Chamber Height: 14 3/4"		
Dimensions*: 34" x 24" x 25"		



DF ROTARY		
Cool final rinse for ready-to-use glassware. Polypropylene conveyor prevents damage to stemware.		
1,000 Glasses/Hour	2.8 Gallons/Min.	Chemical Sanitizing Method
Products: Liquid		
Wash Chamber Height: 10"		
Dimensions*: 39" x 25" x 27"		



OMEGA 5E		
Waist-high loading. Low temp, Energy Star® rating. NSF-certified.		
37 Racks/Hour	0.97 Gallons/Rack	Chemical Sanitizing Method
Products: Liquid		
Wash Chamber Height: 11 1/2"		
Dimensions*: 38" x 24 1/4" x 25 1/4"		

THE ECOLAB DISHMACHINE RENTAL PROGRAM – Smart technology meets outstanding service. The results sparkle.