



TAKE CONTROL WITH THE
FIRST ALL-SOLID, LOW-TEMP
WAREWASHING SYSTEM

SMARTPOWER TSC Single

- ▲ Integrated SMARTPOWER system tracks operational efficiency.
- ▲ Solid SMARTPOWER TSC products deliver unsurpassed cleaning results and greater convenience.
- ▲ Energy Star® rating helps reduce operating costs.

.....


Renting a dishmachine from Ecolab allows you to focus on your business with the security of knowing your warewashing operation is properly managed.

.....



ECOLAB DISHMACHINE RENTAL PROGRAM

The highest level of clean backed by service you can trust.



SMARTPOWER TSC SINGLE SPECIFICATIONS

OPERATING CAPACITY	
Racks per Hour (NSF rating)	40
OPERATING CYCLE (SECONDS) NORMAL	
Wash Time	42
Dwell Time	18
Rinse Time	25
Load Time	5
Total Cycle Time	90
OPERATING CYCLE (SECONDS) HEAVY	
Wash Time	118
Dwell Time	17
Rinse Time	15
Load Time	5
Total Cycle Time	155
OPERATING CYCLE (SECONDS) SUPER HEAVY	
Wash Time	208
Dwell Time	17
Rinse Time	15
Load Time	5
Total Cycle Time	245
OPERATING TEMPERATURES	
Wash (minimum)	120°F
Sanitizing Rinse (minimum)	120°F
WATER CONSUMPTION	
Gallons per Rack	1.02
ELECTRICAL RATINGS	
Wash Pump Motor, Horsepower	3/4 hp
WASH CHAMBER	
Height	17"
WEIGHT	
Machine Weight	230 lb
Shipping Weight	265 lb
UTILITY REQUIREMENTS, ELECTRICAL	
Voltage	115V
Frequency	60Hz
Phase	1 ph
Total Amperage	11.4 A
Minimum Electrical Circuit	15 A
WATER	
Flow (minimum), gal/hour at 100% capacity	60
Waterline Size (minimum)	1/2"
Flow Pressure (recommended)	15-25 psi
Incoming Temperature (minimum)	120°F
Incoming Temperature (recommended)	140°F
DRAIN	
Flow (minimum), gal/min	1
Drainline Size (minimum)	2"

PRODUCTS FOR USE IN THE SMARTPOWER TSC MACHINE



SMARTPOWER
Dishmachine Detergent
6101201 4-6.75 lb
6101202 6-6.75 lb



SMARTPOWER
Rinse Additive All Purpose
6101203 2-2.5 lb



SMARTPOWER Dishmachine
Detergent Heavy Duty
6101200 4-6.75 lb



SMARTPOWER
Rinse Additive Heavy Duty
6101199 2-2.5 lb



SMARTPOWER
Dishmachine Detergent
Specialty
6101308 4-6.75 lb



SMARTPOWER
Solid Sanitizer (US)
6101357 4-1,000
pellet pouches
EPA registered