



**SMARTPOWER**<sup>™</sup>

A complete warewashing program for results that shine, the first time. p 6







	Warewashing4Dishmachine4SMARTPOWER™6Solids8Liquids9Manual Warewashing10Manual Bar Warewashing11Specialty Warewashing11Delimer11Equipment12
	Kitchen Surfaces15Multi-Surface Cleaners15Grill & Fryer Cleaners16Specialty Cleaners17Tools & Accessories18
	Front of House
	Floor Care & Drain Treatment20Floor Care20Drain Treatment21Tools & Accessories21
<b>P</b>	Restrooms24Cleaning Caddy Products & Accessories24Odor Control26Restroom Cleaners & Disinfectants26Tools & Accessories27

	Hand Hygiene	28
	Nexa™ Soaps & Systems	. 28
	Concentrates	. 30
	Syncra™ Soaps & Systems	. 30
	Counter Mount	. 31
	Bulk & RTU	. 31
	Food Preparation	32
	Food Preparation & Rotation	. 32
	Food Safety	. 32
	EcoSure® Solutions	33
	Water & Beverage Quality	34
	Filter Systems & Cartridges	. 34
	Parts & Install Kits	. 36
	Hot Water Filtration	. 36
	Water Softeners	. 36
+	Safety Solutions	37
	CarePod™	
	PPE & Spill Kits	
	Diamana C Cantuallana	20
	Dispensers & Controllers	
_	Warewashing	
	Concentrates	. 39

## Dishmachine



## Optimized operations spotless results

Our high-performance EHT dishmachine reduces downtime with automated procedures, including auto-deliming and tank replenishment. The **high-pressure rinse feature** ensures consistent performance, and our sustainable machine technology can reduce water and energy usage up to 50%.

## EHT

RACKS/HOUR 55

GALLONS/RACK 0.47

**PRODUCTS** 


SANITIZING METHOD:

WASH CHAMBER HEIGHT

SMARTPOWER™/ Solid Power™ XL

181/4"

**VENTLESS OPERATION makes** high-temp warewashing economical.



Ventless operation is achieved through integrated heat recovery technology.

#### See how SMARTPOWER™ adds insightful data and innovative chemistry.

p 6

#### SINGLE DOOR



#### XL-HT

RACKS/HOUR (NSF RATING) 57

GALLONS/RACK (NSF RATING)

0.83

**PRODUCTS** Solid Power™ XL

SANITIZING METHOD: CHEMICAL VS. TEMPERATURE



WASH CHAMBER HEIGHT

17"



#### SMARTPOWER™ TSC Single Rack

(Available in Vapor Vent Option)

RACKS/HOUR (NSF RATING) 46

GALLONS/RACK (NSF RATING)

1.02

PRODUCTS

SMARTPOWER™

WASH CHAMBER HEIGHT

17"

SANITIZING METHOD:



#### ES-2000HT\*

(Available in Vapor Vent Option)

RACKS/HOUR (NSF RATING)

GALLONS/RACK (NSF RATING)

55 1.25

PRODUCTS

Liquid<sup>‡</sup>

SANITIZING METHOD: CHEMICAL VS. TEMPERATURE



WASH CHAMBER HEIGHT

17"



## ES-2000/XL-2000

RACKS/HOUR

GALLONS/RACK 1.02

40

SANITIZING METHOD:



PRODUCTS

Liquid‡/Solid Power™ XL

WASH CHAMBER HEIGHT

17"

#### **DOUBLE DOOR**



#### SMARTPOWER™ TSC Double Rack

RACKS/HOUR

GALLONS/RACK 1.17

SANITIZING METHOD:

78

WASH CHAMBER HEIGHT

PRODUCTS SMARTPOWER™

17"



#### ES-4000/XL-4000

RACKS/HOUR

GALLONS/RACK

1.17

78

SANITIZING METHOD:

WASH CHAMBER HEIGHT

Liquid<sup>‡</sup>/Solid Power<sup>™</sup> XL

17"

**‡ CLDS Compatible** 

<sup>\*</sup> Available in US Only

## Dishmachine CONTINUED



#### **CONVEYOR**



#### SMARTPOWER™ Conveyor 44

RACKS/HOUR 200

GALLONS/RACK

SANITIZING METHOD:

0.57

PRODUCTS SMARTPOWER™ WASH CHAMBER HEIGHT

171/211



#### EC-44/EC-44HH\*

RACKS/HOUR 244

GALLONS/RACK

0.91

SANITIZING METHOD:



**PRODUCTS** 

SMARTPOWER™/ Solid Power™ XL

WASH CHAMBER HEIGHT

18"/ 25" (HH)



SMARTPOWER™ Conveyor 66 RACKS/HOUR 200

GALLONS/RACK 0.57

SANITIZING METHOD:

PRODUCTS

SMARTPOWER™

WASH CHAMBER HEIGHT

171/2"

EC-66/EC-66HH\*

RACKS/HOUR (NSF RATING) 244

GALLONS/RACK (NSF RATING) 0.91

SANITIZING METHOD: CHEMICAL VS. TEMPERATURE

PRODUCTS

SMARTPOWER™/ Solid Power™ XL

WASH CHAMBER HEIGHT

18"/ 25" (HH)

Keep your machine clean and shiny with stainless steel cleaners.

p 17

#### UNDERCOUNTER/GLASSWARE



#### U-HT<sup>†</sup>

RACKS/HOUR (NSF RATING) 30

GALLONS/RACK 0.78

SANITIZING METHOD:



PRODUCTS Liquid

WASH CHAMBER HEIGHT 143/4"

#### **DF Rotary**

RACKS/HOUR

GALLONS/RACK

2.8 1000 glasses/hr gal/min

PRODUCTS Liquid

SANITIZING METHOD:



WASH CHAMBER HEIGHT

10



#### U-LT<sup>††</sup>

RACKS/HOUR (NSF RATING) 21

GALLONS/RACK 1.6

SANITIZING METHOD: CHEMICAL VS. TEMPERATURE



PRODUCTS Liauid<sup>‡</sup>

WASH CHAMBER HEIGHT 143/4"



#### Omega 5E

RACKS/HOUR (NSF RATING) GALLONS/RACK

> 31 1.16

SANITIZING METHOD: CHEMICAL VS. TEMPERATURE



**PRODUCTS** Liquid<sup>‡</sup>

WASH CHAMBER HEIGHT 111/2"

Racks, curtains and other parts available for your dishmachine.

p 12

Point of Use Softener available for extreme hard water conditions.

<sup>\*</sup> Requires Booster <sup>†</sup> Canada 501-HT



## SMARTPOWER™



## Complete warewashing solutions

By combining our **innovative chemistry and personalized** service with our ability to **collect data and develop actionable insights**, SMARTPOWER™ brings you better transparency and control across your entire warewashing operation. Enjoy a new level of performance excellence and ensure your guests never see less than impeccable wares.

**Insightful data** from the SMARTPOWER™ controller gives full visibility.

p **38** 

#### **DETERGENT**



#### SMARTPOWER<sup>™</sup> Dishmachine Detergent

High performing machine warewashing detergent for use in soft to moderate water conditions, and effective on all types of food soils. Its concentrated formula and powerful chemistry is non-corrosive, and 99.7% phosphate free. It is effective on all dishware.

6101201 4-6.75 lb 6101202 6-6.75 lb



#### SMARTPOWER™ Dishmachine Detergent Heavy Duty

Highest performing, low-phosphorus solid detergent in the industry for hard water and heavy soils. Use with the toughest soil and water conditions.

6101200 4-6.75 lb



#### SMARTPOWER™ Dishmachine Detergent Metal Safe

Solid machine detergent for washing aluminum and other soft metals. Works best in soft to moderate water conditions and light to heavy soil conditions.

6101307 4-6.25 lb



# SMARTPOWER<sup>™</sup> Dishmachine Detergent Specialty

High performing, low-phosphorous, chlorine free detergent for use in regular soil and soft to moderate water conditions. Helps manage total costs by helping to reduce rack waste.

6101308 4-6.75 lb



#### SMARTPOWER™ Manual Detergent

Solid detergent with a modern scent, for use in 3-compartment sinks. Cuts through the toughest food soils and thickest grease to clean pots and pans efficiently, with minimal scrubbing and at the lowest cost. No measuring or pouring by hand, no spillage, and no waste. Mild on hands.

6101907 2-3 lb

## SMARTPOWER™ CONTINUED

#### RINSE ADDITIVE



#### SMARTPOWER™ Rinse Additive All Purpose

High performing machine rinse additive for use in normal water conditions. Its concentrated formula and powerful chemistry is noncorrosive, and 99.7% phosphate free reducing the need for hand polishing with spot-free performance.

6101203 2-2.5 lb



#### SMARTPOWER™ Rinse Additive Heavy Duty

High performing machine warewashing rinse additive for use in water hardness over 8 grains. Its concentrated formula and powerful chemistry is non-corrosive, and 99.7% phosphate free reducing the need for hand polishing with spot-free performance.

6101199 2-2.5 lb

#### **SANITIZER**



#### SMARTPOWER™ Sanitizer

Solid sanitizer that is effective across a wide efficacy range with no rinse required on food contact surfaces. For sanitizing of equipment, utensils, and work or dining surfaces.

6101355 (US) 2-2 lb 6101351 (Canada) 2-2 lb



#### SMARTPOWER™ Dishmachine Sanitizer

For sanitizing hard, non-porous food contact surfaces including eating establishment equipment/utensils, milkshake machines & soft serve ice cream machines and food processing plant premises and equipment.

6101357 (US) 4-100 tablet 6101398 (Canada) 4-100 tablet

#### PRESOAK



#### SMARTPOWER™ Presoak Cutlery/Flatware

Unique combination of alkalinity and surfactants loosens soils and emulsifies grease. Patented dualenzyme formula removes tough, dried or baked-on protein and starch soils, reducing the need for multiple rewashes.

6101890 3-4 lb



#### SMARTPOWER™ Presoak Pot and Pan

Specifically formulated to remove heavy soils prior to dishmachine washing. Designed to be safe on hands while effectively removing blackened carbonized build-up and adding metal protection to prolong the life of pots and pans. Solid alkaline formula removes greasy, baked-on soils.

6101353 3-5 lb 6101352 6-5 lb

**SMARTPOWER™** blocks are shapeand color-coded for easy dispensing. Learn more about SMARTPOWER™ dispensers.

## **Solids**

#### **DETERGENT**



#### Solid Power™ XL

Ultra-high activity for more dishes per capsule than any other solid detergent in the industry.

6100185 4-9 lb 6100183 (US only) 2-9 lb



#### Solid Super Impact™

For your toughest conditions, a highly active set of ingredients and three times the chlorine for exceptional cleaning and destaining performance.

6110256 4-9 lb



#### Solid Metal Pro™

Powerful cleaning for soft metals with improved safety over liquids.

6110751 4-8 lb



#### Solitaire™

Tough on soils for quick cleaning of pots and pans.

6117301 4-5 lb 6110884 (US only) 2-5 lb



#### Solid Ultra Dishmachine Detergent

Solid Ultra Dishmachine detergent is a good entry level solid machine detergent. A high performing, low phosphorous formula that provides excellent results even in challenging water conditions.

6100995 (Canada only) 4-3.63 kg

**Learn more about** reducing waste and controlling costs with proper dilution & dispensing systems.

p **39** 

#### PRESOAK



#### Silver Power™

Flatware presoak softens dried-on soils for maximum cleaning results in the dishmachine.

6112922 2-8 lb



#### DeCarbonizer MXP™ Soak Tank Activator

Powerful soaking solution removes greasy, cooked on soils from pots and pans.

6114415 (US only) 2-8 lb

#### RINSE ADDITIVE



#### Solid Brilliance™

Reduces spotting for sparkling results in most water conditions.

6125395 2-2.5 lb

## Liquids

#### DETERGENT



# Concentrated Liquid Dishmachine Detergent\*

Highly concentrated detergent, integrated dispensing, lockout fitment.

6100968 (US only) 1-2.5 gal



#### Heavy Duty Liquid Dishmachine Detergent

Use with the toughest soil loads and water conditions. Use on tough food soils on all dishware.

6100640 (Canada only) 4-3.78 L 6100641 (Canada only) 1-18.9 L



#### Ultra-Klene™

Powerful, proven cleaning of all soils to help minimize costly rewash.

6113326 4-1 gal 6112716 1-5 gal



#### Ultra-Klene™ Plus

The benefits of Ultra-Klene $^{TM}$  with added performance for hard water.

6112807 1-5 gal



#### Super Trump™

Outstanding cleaning results for glass washers where appearance is key.

6112740 4-1 gal 6112757 1-5 gal

#### RINSE ADDITIVE



#### Ultra Dry™ Rinse Additive

Reduces spotting and dry time in low-temp machines for higher efficiency.

6113722 4-1 gal 6115172 1-4.5 gal



#### Rinse Dry™

Reduces spotting and dry time in high-temp machines for higher efficiency.

6110942 4-1 gal 6110934 1-5 gal



#### Fast Drying Rinse Additive

Fastest drying rinse additive in the industry. Ideal for plasticware.

6100118 2-5 gt



#### R-O Free<sup>™</sup> Rinse Additive

Makes spots disappear in challenging, hard or high-TDS water conditions.

6117532 2-5 gt

<sup>\*</sup> Products only available with Ecolab Dishmachine Program (EDP)



## Liquids continued

#### SANITIZER



#### Concentrated Sanitizing Rinse\*

Highly concentrated sanitizer\*\* with rinse aid properties, integrated dispensing, lockout fitment.

EPA Reg. No. 1677-244

6100804 (US only) 1-2 gal



#### Ultra San™

Chlorine sanitizer for low-temp machines.

EPA Reg. No. 1677-52

6113961 (US) 1-5 gal 6101059 (Canada) 1-18.9 L 6110491 (Canada) 4-4 L



#### Eco-San™

Chlorine sanitizer for all lowtemp machines.

EPA Reg. No. 1677-52

6113979 (US only) 4-1 gal



#### Mikroklene™

lodine sanitizer for low-temp glass washers and hard surfaces.

6110511 (Canada) 4-4 L

## Manual Warewashing



#### Scout™

Concentrated liquid with ready-to-use dispensing, creates lasting suds.

6110906 2-2 gal



#### Liquid Pot & Pan Detergent

Safer Choice Certified. For customers who prefer an eco-certified manual detergent.

6100320 (US only) 1-5 gal 6100796 (US only) 1-15 gal



#### Pantastic™

Ready-to-use. Is a nonphosphate, liquid pot and pan detergent that cuts through grease. Suds are long lasting, even in the presence of grease and other heavy food soils, but remains gentle on hands.

6113003 9-32 fl oz 6112963 4-1 gal 6112971 1-5 gal



#### Monsoon

Low-foaming liquid detergent for use in recirculating sinks.

6113505 1-5 gal



#### Liquid Assure™

Safer Choice Certified. Concentrated liquid presoak for removing soils on flatware.

6101083 4-1 gal

<sup>\*</sup> Products only available with Ecolab Dishmachine Program (EDP)

<sup>\*\*</sup> Peroxyoctanoic Acid (POOA)

## Manual Bar Warewashing









#### Bar Dandy™

Low-foaming liquid detergent for use in bar glass washers.

6114050 (US only) 4-1 gal

#### Manual Bar Glass Detergent

Ready-to-use, low-foaming detergent helps get glasses clean while protecting beverage quality.

6110372 (US only) 100-0.5 oz packets

#### Manual Bar Glass Sanitizer

EPA registered sanitizer and disinfectant can be used in bars, restaurants, hotels and on food contact surfaces. Helps ensure optimal beverage taste and appearance.

EPA Reg. No. 65169-1-1677

6110269 (US only) 100-0.25 oz

#### MANUAL BAR TOOLS



#### Barmaid Submersible Motorized Pub Scrub

6½" Brushes 96218285 5-Pack

Replacement Brushes

96218292 5-Pack



#### Manual Triple Glass Washer

8" Brushes 96218243 3-Pack

Replacement Brushes

96218318 (US only) 5-Pack

## Specialty Warewashing



#### Specialty Beverage Cleaner

Unit-dose tablets combat tea and coffee stains in brewing equipment. Compatible for a wide range of beverage equipment models

6100357 (US only) 1-100 tablets



#### Dip-it™ XP

Destainer for coffee, tea and other tough-to-remove stains.

6117583 8-1.75 lb

## Delimer



#### Lime-A-Way™

A versatile multi-purpose lime scale remover that maximizes dishmachine performance.

6101131 4-1 gal



#### Solid Lime-A-Way™

Eliminates chemical splashing while attacking rust and iron stains.

6115905 (US only) 6-1.33 lb



#### Clinging Lime-A-Way™

A clinging gel lime scale removal for tough-to-reach applications.

6115210 6-32 fl oz



#### Lime-A-Way™ Select

Safer Choice Certified. Eco-certified delimer delivers top performance.

6100823 (US only) 4-1 gal

## Equipment



Full-Size Glass Racks

Contact your Ecolab representative.



Half-Size Glass Racks

Contact your Ecolab representative.



Full-Size Cup Racks

Contact your Ecolab representative.



Plate Master Racks™

Contact your Ecolab representative.



## Full-Size Silverware Rack

High-quality resin and design prolong life of flatware rack and reduce equipment expenses. Inside height: 35%".

Brown 9293-7507 1 each Beige 9293-7515 1 each



#### Full-Size Open Rack

Open grid design provides ideal results for virtually all medium to large items. Inside height:  $3\frac{5}{8}$ ".

Brown 9291-8002 1 each Beige 9291-8010 1 each



#### Highwall Plate Rack

Sturdy rack holds plates at correct angle for optimal washing. Inside height: 35%".

Brown 9295-7059 1 each Beige 9295-7067 1 each



#### Highwall Starter Kit

This kit comes with two plate racks, one silverware rack and one open rack.

Brown 9293-1054 1 kit Beige 9293-1062 1 kit



#### Open-End Peg Rack

Pegs hold trays at proper angle for thorough, one-pass results. Holds 8 trays less than 18" or 6 longer trays.

Beige 9295-7505 1 each



#### Latched Ramekin Rack

Soufflé cup rack with hinged lid is specifically designed to maximize cleaning performance for small items that jump out of ordinary racks during the washing cycle. 1½" high.

Brown 9291-1833 1 each



# Open-End Sheet Pans & Insulated Tray Racks

Maximize rack load and achieve superior results. Racks reduce pan-tray wash costs up to 80% by positioning wares at correct angle to minimize rewash.

4 sheet pans	9295-0112	1 each
5 bun pans	9295-1136	1 each
4 insulated trays	9291-1858	1 each
6 insulated trays	9291-1866	1 each

#### For additional rack sizes and models,

contact your Ecolab representative.

## Equipment CONTINUED





#### SortMaster™ Breakdown Station Cart

Stainless steel cart allows employees to sort and rack soiled wares on location.

SortMaster<sup>™</sup> Breakdown Station

9290-1974 1 each

SortMaster™ Complete Package

9290-8235 (US only) 1 each

(Includes SortMaster™ Breakdown Station and Silvermaster™ System Starter Set - 9290-6023)



#### Soak Master™

Heavy-duty spray valves with knife-like spray to cut through debris.

Soak Master™ with dolly & handle	9290-1487	1 each
Soak Master™ with dolly	9290-1479	1 each
Soak Master™ tank	9298-2016	1 each
Soak Master™ drain ball valve	9298-3873	1 each
Soak Master™ vinyl cover	9295-2829	1 each



#### Wastewell Dollies

Catch excess drainage water to reduce accidents and unwanted spills. Holds one stack of 20" full racks or two stacks of 10" half racks. Comes with 4" casters.

Brown	9290-1149	1 each
Blue	9290-1004	1 each
With handle	9290-6114	1 each



#### Silvermaster™ Starter Set

Sort tableware at the dish table with this space-saving silverware management system.

3 Soak Pans, 6 Silverware Carrier Washers, 3 Cylinder Washers, 8 Round Silverware Baskets 9290-6023 1 set



#### Rack Shelf™

Made of high-impact ABS plastic, this shelf is perfect for operations with limited space. Measures 16" H x 22" W x 161/4" L.

Rack Shelf™ with Drain Kit	9290-2386	1 each
Drain Kit	9290-1081	1 each



#### Rack Covers

Protects sanitized ware from soils. Translucent cover makes it easy to identify contents.

12" high	9290-8243	1 each
36" high	9290-8250	1 each



## Equipment CONTINUED



**Dishmachine Curtains** 

Contact your Ecolab representative.



#### Dishmachine Replacement Parts

Contact your Ecolab representative.



#### Replacement Hoses, Stainless Steel

High-quality, stainless steel hose optimizes water flow and minimizes risk of leaks.

20"	9297-3544	1 each
44"	9297-3502	1 each
68"	9297-3551	1 each



#### Replacement Gooseneck Spring

Engineered to prolong life of stainless steel hoses. Enables convenient use and storage of pre-rinse units.

9297-0037 1 each



#### Low Flow Faucet Aerator

Helps save water every time you run the faucet. 0.59pm aerator that provides 77% water savings compared to a standard 2.29pm aerator.

8531-0028 1 each



#### **Eco-Spray**

Turns on with a pull of the hand grip, no trigger. Heavy-duty, 60", 200 psi hose.

9295-2589 1 each



#### JetSpray Valve

Smart, one-handed trigger lock with heat insulated touch points.

B-2108	9655-2141	1 each
B-21080	(US only)	
	9655-2099	1 each



#### Spray Valves

Heavy-duty spray valves with knife-like spray to cut through debris.

Pre-Rinse Spray Valve

9297-2470 1 each Low-Flow Spray Valve (B-0107J)

9297-2023 1 each

Low-Flow Spray Valve (B-0107C) (US only) 9297-2019 1 each

Heavy-Duty Spray Valve (1.6 GPM) (US only) 9297-2037 1 each

9297-2037 1 each Heavy-Duty Spray Valve (1.2 GPM)

9297-2032 1 each PowerPulse™ High Efficiency

Spray Valve (0.74 GPM)

8524-3507 1 each

**Tools & accessories** for your Manual Bar program are available.

## **Multi-Surface Cleaners**





## No Rinse Food Contact Cleaner Sanitizer

One product to clean and sanitize hard, non-porous food contact surfaces. **Eliminates 99.9%** of *Staphylococcus aureus* and *Klebsiella pneumoniae* in **60 seconds**.

EPA Reg. No. 6836-138-1677

6101140 (US only) 2-2 L

Confirm sanitizer concentration levels with QT Test Strips.

p 18



#### Peroxide Multi Surface Cleaner & Disinfectant

One product to clean and disinfect all hard surfaces and glass for entire restroom and front of the house. EPA registered disinfectant with kill time as short as 3 minutes, killing norovirus as fast as 45 seconds (when diluted at 6 oz/gallon).

EPA Reg. No. 1677-238, DIN 02412314

6100693 (US) 1-2 gal 6100791 (US) 2-2 L 6100894 (Canada) 1-7.6L 6100897 (Canada) 2-2 L



#### Peroxide Multi-Surface Cleaner

Green Seal™ and USDA Certified Bio-Based product offers excellent cleaning and leaves a streak-free performance on glass and hard surfaces.

6100302 1-2.5 gal 6100925 2-2 L



#### Oasis<sup>™</sup> 146 Multi-Quat Sanitizer

EPA/DIN registered sanitizer with wide efficacy range. (US: 150-400 ppm; Canada: 200-400 ppm)

EPA Reg. No. 1677-198, DIN 02279398

6117781 (US) 4-1 gal 6100536 (US) 1-2.5 gal 6117718 (US) 1-15 gal 6110384 (Canada) 1-9.46 L 6100011 (Canada) 4-3.78 L



#### 14 Plus Antibacterial All Purpose Cleaner

Light duty all-purpose cleaner and disinfectant for hard surfaces. EPA registered disinfectant with kill times as fast as 3 minutes.

EPA Reg. No. 6836-349-1677

6100920 (US only) 1-2.5 gal 6100912 (US only) 2-2 L



#### Oasis Pro 14 Antibacterial All Purpose Cleaner & Disinfectant

Light duty all-purpose cleaner and disinfectant for hard surfaces. EPA registered disinfectant with kill times as fast as 3 minutes.

DIN 02248419

6100116 (Canada only) 2-2 L

**Learn more about** reducing waste and controlling costs with proper dilution & dispensing systems.



## **Grill & Fryer Cleaners**



## Greaselift™

Effective degreaser that require no gloves or goggles to clean ovens, grills, stove hoods and vents.

6100155 2-2 L 6100284 6-32 fl oz



#### Grease Express™ Fast Foam Degreaser

Foaming degreaser clings to vertical surfaces, quickly dissolving and suspending greasy oils.

6110123 4-1 gal 6110126 6-32 fl oz



#### Greasestrip Plus™

High-performance clinging gel degreaser effective on ovens, grills, stove hoods, vents and broilers.

6119505 4-1 gal 6129777 6-32 fl oz



#### Greasecutter Plus™

Heavy-duty cleaner and degreaser. 6119513 (US only) 4-1 gal



#### Grease Express™ High Temp Grill Cleaner

Fast-acting formula quickly removes grease and grime from grill tops.

6110251 60-3.6 fl oz 6110127 6-32 fl oz



#### Grease Express™ No Boil Fryer Cleaner

Grease Express No Boil Fryer Cleaner is a ready-to-use (RTU) deep fryer cleaner formulated to remove cooked-on carbon and grease in less time, with safer procedures, supporting fried food quality and taste at a lower total cost.

6101929 4-24 fl oz



#### Grease Express™ High Temp Grill Cleaner Starter Kit

Everything needed to quickly clean grease and grime from grill tops.
Kit contents: No-scratch grill polisher and 6 pads, grill squeegee, procedures CD for training and Grease Express™
Hi-Temp Grill Cleaner 10-3.6 oz packets.

6110378 1 kit



p 21



#### Grease Express™ Fryer Cleaner

Safely removes carbonized grease inside the fryer quickly and easily. Extends fryer oil-life and improves food quality.

6110307 26-8 oz



#### Specialty Oven Cleaner

Oven cleaner specifically designed to break up grease and lift up soils from surfaces of specialty ovens.

6100704 1-2.5 gal



#### Specialty Oven Rinse RTU

Oven rinse used to delime specialty ovens after the final step in the cleaning process.

6100705 1-2.5 gal



#### Super Cling Degreaser

Super Cling Degreaser is a specialty PPE-free degreaser with superior cling that is approved for use on Merrychef® ovens.

6101358 (US only) 4-32 fl oz

## **Specialty Cleaners**

#### **STAINLESS**



#### Eco Shine

Water-based stainless steel cleaner and polish.

6118440

6-32 fl oz



#### Medallion™

Ready-to-use cleaner and polish removes light soil and restores sheen. Protective luster helps keep out soil and moisture. Safe on all metal surfaces and kitchen equipment.

6118424 6-32 fl oz



#### Stainless Steel Cleaner and Polish

Removes light soil and restores sheen to all metals. Protective barrier guards against soil and moisture and leaves no oily residue.

6100467

12-17 fl oz

#### **BACK DOCK**



#### Oasis™ Caravan Mobile Unit

Cleans greasy, oily areas and neutralizes malodors.

9215-1243 1 each



#### Oasis™ Outback Wall Mount

Wall mount dilution system specifically for exterior use.

9215-1004

1 each



#### Oasis<sup>™</sup> 902

An exterior multi-surface foaming degreaser designed to clean greasy, oily areas such as loading docks, garbage containers and other exterior surfaces.

6118405 1-2.5 gal



#### Oasis<sup>™</sup> 904

An exterior heavy-duty water soluble odor counteractant to effectively neutralize all malodors associated with garbage. Designed to be used with Oasis™ 902.

6118411 1-2.5 gal

Selection of **Personal Protective Equipment** available.



## Specialty CONTINUED

#### SPECIALTY CLEANERS



#### Kool-Klene™ No Thaw Freezer Cleaner

Quick drying liquid freezer cleaner. Great for cleaning freezer floors.

6115461 4-1 gal

Trigger Sprayers

92652354 12 pack

**Extended Trigger Sprayers** 

9263-1399 12 pack



#### Sani Glide

A soap-based detergent lubricant for conveyors. It performs efficiently at low foam levels and mixes completely in cold water regardless of water hardness.

6101159 (Canada only) 1-18.9 L



#### **Burnishing Compound**

Burnishes fine silverware (for use in burnishing machines).

6170101 4-1 gal



#### Triplet<sup>™</sup> Plus

Cleaner and sanitizer for soft serve ice cream machines. Removes milkstone and protein buildup.

EPA Reg. No. 5389-15-1677

6117380 (US only) 50-1 oz packets



#### Klenz-Glide™ 10

Lubricant and cleaner to keep foodservice conveyors clean and extend conveyor life.

6114126 (US only) 1-5 gal

## Tools & Accessories



#### Sanitizer Pail

Ergonomic plastic handles, recessed base for splash reduction and slanted lip for easier pouring. Durable, wear resistant ink meets health department requirements.

Sanitizer Pail

60503-12-31 (US) 92681001 (Canada) 1 each 60503-42-31 (US) 10042221 (Canada) 6-Pack

Detergent Pail

60504-12-31 (US) 92681003 (Canada) 1 each 60504-42-31 (US) 10042224 (Canada) 6-Pack



#### QT-40 Test Strips

Confirms sanitizer concentration levels to help ensure compliance.

20304-05-11 (US)

92682248 (Canada) 1-15 ft roll



#### Sanitizer Testing Station

Promotes proper chemical sanitation and helps reduce Health Department fines. Holds four test tape dispensers and four vials.

20312-01-00 (US)

92212391 (Canada) 1 each



#### Interlocking Bar Mat

12" x 12"

92972082 1 each



#### Interlocking Bar Mat Strips

3½" x 12"

92972074 1 each

#### Front of House





## Peroxide Multi Surface Cleaner & Disinfectant

One product to clean and disinfect all hard surfaces and glass for entire restroom and front of the house. EPA registered disinfectant with kill time as short as 3 minutes, killing norovirus as fast as 45 seconds.\*

EPA Reg. No. 1677-238, DIN 02412314.

6100693 (US) 1-2 gal 6100897 (Canada) 2-2 L

\*When diluted at 6 oz/gallon.



#### No Rinse Food Contact Cleaner Sanitizer

One product to clean and sanitize hard, non-porous food contact surfaces. Eliminates 99.9% of Staphylococcus aureus and Klebsiella pneumoniae in 60 seconds.

EPA Reg. No. 6836-138-1677

6101140 (US only) 2-2 L



#### Peroxide Multi-Surface Cleaner

Green Seal™ and USDA Certified Bio-Based product offers excellent cleaning and leaves a streak-free performance on glass and hard surfaces.

6100302 1-2.5 gal 6100925 (Canada only) 2-2 L



#### 14 Plus Antibacterial All Purpose Cleaner

Light duty all-purpose cleaner and disinfectant for hard surfaces. EPA registered disinfectant with kill times as fast as 3 minutes.

EPA Reg. No. 6836-349-1677 6100920 (US only) 1-2.5 gal



#### Oasis Pro 14 Antibacterial All Purpose Cleaner & Disinfectant

Light duty all-purpose cleaner and disinfectant for hard surfaces. EPA registered disinfectant with kill times as fast as 3 minutes.

DIN 02248419

6100116 (Canada only) 2-2 L



#### Orange Force<sup>™</sup> (Oasis<sup>™</sup> 137)

Multi-purpose alternative for cleaning greasy soils, film, and smoke from multiple surfaces.

6114559 1-2.5 gal 6115636 (US only) 6-32 fl oz



#### Glass Cleaner

Streak-free, fast-drying performance on windows, mirrors, glass, plastic, acrylics and painted surfaces. USDA Certified Bio-Based product.

6100288 1-2.5 gal





#### Wet Wipe Blue Towel

61111-01-00 (US) Pack of 150 92682324 (Canada) Pack of 150

For cleaning non-food spills/accidents, use our **Biohazard Response Kit**.

р **37** 



#### Oasis Pro™ Microfiber Cloths

Blue	9621-2290	1-12 pk
Pink	9621-2292	1-12 pk
Yellow	9621-2293	1-12 pk

## Floor Care



# Find DuraLoc™ products

p 22-23

## The ultimate floor cleaning system

To get the job done right, you need the proper tools. That's why Ecolab offers this revolutionary line of **durable, long-lasting** interlocking floor cleaning products. DuraLoc™ tools and Ecolab floor cleaners work together to give you the ultimate clean in less time – and **at a lower cost.** 

#### Sanitizing Wash 'n Walk™ No-Rinse Floor Cleaner

The industry's best enzymatic, no-rinse cleaner helps prevent grease buildup.

EPA Reg. No. 1677-239

6100731 (US) 1-2.5 gal 6100734 (US) 1-15 gal 6100778 (Canada) 1-9.46 L





#### No/Low Maintenance Flooring Cleaner and Protector

Patent pending technology specially designed for Luxury Vinyl Tile (LVT), laminate, rubber and other low maintenance floors. This unique, daily-use formula will clean, repair minor scratches and resist dulling of the floor.

6101941 1-2.5 gal 6101943 2-2 L 6101946 6-64 oz



# Oasis™ 125XP (Acid)

6110625

Oasis™ 115XP (Alkaline)

Acid kitchen floor cleaner designed to remove mineral soils.

Extra strength alkaline, floor cleaner for dissolving and emulsifying greasy soils.

1-2.5 gal

6110648 (US) 1-2.5 gal 6120390 (Canada) 1-9.46 L



#### Oasis<sup>™</sup> 100 Neutral Floor Cleaner

Neutral citrus all-purpose cleaner concentrate for daily cleaning of all hard floors including wood, stone and vinyl.

6114522 1-2.5 gal 6119554 (US only) 15 gal



#### Oasis™ Enforce (Chlorinated-Alkaline)

Self-foaming chlorinated-alkaline kitchen floor cleaner for mop-bucket use.

6114696 1-2.5 gal

**Easy-to-use**, controlled dispensing with the Oasis System.

#### Floor Care CONTINUED





#### Pinnacle<sup>™</sup> Intensive Tile Cleaner

Removes stubborn soils and grease from ceramic tiles and grout.

6170211

4-1 gal



#### Revitalize™ Miracle Spotter

"Go-to" spotter that is ideal for unknown soils. Safe for all carpet types. Safer Choice Certified.

6101125

4-22 oz



#### Revitalize™ Chewing Gum Remover

Easily and effectively freeze gum or candle wax and quickly chip it away.

6101161 (Canada)

12-148 mL

## **Drain Treatment**



#### Ecolab Pump-Up Foamer

Convenient foamer to apply Sanitizing Wash 'n Walk™ into drains for controlling fruit fly feeding and breeding grounds and malodors.

9215-3307

1-1.3 gal



#### Pathways™ Beverage Drain Control

Quickly dissolves sugar snakes (bacterial cellulose buildup) in beverage dispenser drains and helps prevent its recurrence.

6101141

2-64 oz



#### Pathways™ Drain Treatment

Biological grease digestant helps automatically maintain drains, lines and grease traps.

6129810

1-2.5 gal



#### Bingo™ Liquid Drain Cleaner

Reaches and effectively dissolves hair, protein, grease, oil and soap.

6135112

12-32 fl oz



#### Pathways™ Solid Drain Sanitizer

Patented water-activated, time-release formulation helps provide controlled sanitizing in floor drains.

EPA Reg. No. 1677-134

6120108 (US) 1 6301797 (Canada) 1

12-4" (118 mL) rings 12-4" (118 mL) rings

## **Tools & Accessories**



#### **Grease Proof Mat**

Ideal for areas exposed to grease and high traffic. Raised surface ribs and bottom grippers reduce trip hazards. 1-3'  $\times$  5'  $\times$   $\frac{1}{2}$ ", black.

9297-2018

1 each



#### Mobile Mat Rack

Transports mats quickly and easily from workstations to cleaning areas. Holds up to ten 3' x 5' commercial mats, with a load capacity of 500 lbs. 1-42" x 28" x 40".

9299-2000

1 each



## Tools & Accessories continued



#### DuraLoc™ Dual Cavity Mop Bucket

This rugged mop bucket features separate compartments for the cleaning solution and for dirty water, helping to eliminate contamination for a better clean.

Blue	61702-01-31 (US)	92682567 (Canada)	1 each
Yellow	61702-02-31 (US)	92682568 (Canada)	1 each
Red	61702-03-31 (US)	92682574 (Canada)	1 each
Green	61702-05-31 (US)	92682576 (Canada)	1 each
Gray	61702-09-31 (US)	92682575 (Canada)	1 each



#### DuraLoc™ Universal Insert Holder

Connects DuraLoc<sup>™</sup> tool inserts to DuraLoc<sup>™</sup> handles. Sturdy, long-lasting construction. Required for DuraLoc<sup>™</sup> Mops, Squeegees, and Angle Brooms.

61713-00-00 (US) 92682616 (Canada) 1 each

#### MOPS



#### DuraLoc™ Grease Release Mop

The Grease Release Mop Insert has been proven to significantly improve floor traction. Requires DuraLoc $^{\mathbb{M}}$  Universal Insert Holder and DuraLoc $^{\mathbb{M}}$  Handle.

Blue	61700-01-00 (US)	92682556 (Canada)	1 each
Yellow	61700-02-00 (US)	92682557 (Canada)	1 each
Red	61700-03-00 (US)	92682558 (Canada)	1 each
Green	61700-05-00 (US)	92682559 (Canada)	1 each
Gray	61700-09-00 (US)	92682560 (Canada)	1 each



#### DuraLoc<sup>™</sup> 17 oz. Looped End Mop

Designed to offer superior performance at a great value. Requires DuraLoc™ Universal Insert Holder and DuraLoc™ Handle.

Blue	61700-11-00 (US)	92682561 (Canada)	1 each
Yellow	61700-12-00 (US)	92682562 (Canada)	1 each
Red	61700-13-00 (US)	92682563 (Canada)	1 each
Green	61700-15-00 (US)	92682564 (Canada)	1 each
Gray	61700-19-00 (US)	92682565 (Canada)	1 each

#### **BROOMS**



#### DuraLoc™ Angle Broom Insert

Durable, long-lasting polyester bristles. Requires DuraLoc™ Universal Insert Holder and DuraLoc™ Handle.

Blue Yellow	61704-01-00 (US) 61704-02-00 (US)	92682551 (Canada) 92682552 (Canada)	1 each 1 each
Red	61704-03-00 (US)	92682553 (Canada)	1 each
Green	61704-05-00 (US)	92682554 (Canada)	1 each
Black	61704-07-00 (US)	92682555 (Canada)	1 each



#### DuraLoc™ Outdoor Sweep

Long-lasting polyester bristles make this a durable broom. Requires DuraLoc™ Handle.

Blue	61705-01-00 (US)	92682592 (Canada)	1 each
Yellow	61705-02-00 (US)	92682593 (Canada)	1 each
Red	61705-03-00 (US)	92682594 (Canada)	1 each
Green	61705-05-00 (US)	92682595 (Canada)	1 each
Black	61705-07-00 (US)	92682596 (Canada)	1 each

#### **SQUEEGEES**



#### DuraLoc™ Squeegee Insert, Moss Foam

Foam material works on all types of surfaces. Requires DuraLoc™ Universal Insert Holder and DuraLoc™ Handle.

Blue	61706-01-31 (US)	92682597 (Canada)	1 each
Yellow	61706-02-31 (US)	92682598 (Canada)	1 each
Red	61706-03-31 (US)	92682599 (Canada)	1 each
Green	61706-05-31 (US)	92682600 (Canada)	1 each
Black	61706-07-31 (US)	92682601 (Canada)	1 each



#### DuraLoc™ Squeegee Insert, Rubber

Durable, long-lasting material works best on smooth surfaces. Requires DuraLoc™ Universal Insert Holder and DuraLoc™ Handle.

Blue	61706-11-00 (US)	92682602 (Canada)	1 each
Yellow	61706-12-00 (US)	92682603 (Canada)	1 each
Red	61706-13-00 (US)	92682604 (Canada)	1 each
Green	61706-15-00 (US)	92682605 (Canada)	1 each
Black	61706-17-00 (US)	92682606 (Canada)	1 each

## Tools & Accessories continued



#### **BRUSHES**



#### DuraLoc<sup>™</sup> Deck Brush

Strong polyester bristles and extra stiff center bristles. Requires DuraLoc™ Handle. Use with optional Big Dipper.

Blue	61702-01-00 (US)
	92682587 (Canada
Yellow	61702-02-00 (US)

92682587 (Canada) 1 each 61702-02-00 (US) 92682588 (Canada) 1 each

1 each

1 each

1 each

92682588 (Canada) Red 61702-03-00 (US)

92682589 (Canada)

Green 61702-05-00 (US)

92682590 (Canada) 1 each Black 61702-07-00 (US)

92682591 (Canada) 1 each



#### DuraLoc™ Mop Brush

The DuraLoc™ Mop Brush attaches easily to the Universal Insert Holder and improves cleaning while mopping.

61701-01-00 (US) 92682566 (Canada)

1 each



#### DuraLoc<sup>™</sup> Big Dipper<sup>™</sup>

Fits into DuraLoc™ Deck Brush and helps ensure the correct dispensing of floor cleaning chemical. Requires DuraLoc™ Universal Insert Holder, DuraLoc™ Deck Brush, and DuraLoc™ Handle.

61703-00-00 (US)

92682586 (Canada) 1 each

**Upgrade your floor mats** to help reduce slips, trips and falls.

p **21** 

#### **HANDLES**



#### DuraLoc™ Zone Color Sleeve, Long

Colored sleeve fits on  $\mathsf{DuraLoc}^\mathsf{m}$  handles for color coding and zone isolation.

Blue	61707-01-00 (US)

92682607 (Canada) 1 each Yellow 61707-02-00 (US)

rellow 61707-02-00 (US) 92682608 (Canada)

Red 61707-03-00 (US)

92682609 (Canada)

Green 61707-05-00 (US)

02692610 (Canada

92682610 (Canada) 1 each



#### DuraLoc™ 54" Straight Handle, Lightweight

Lightweight aluminum construction. Fits DuraLoc™ tools.

61709-01-00 (US)

92682612 (Canada) 1 each



#### DuraLoc™ 54" Straight Overmold Handle

Durable handle made from aluminum core with plastic over-mold. Fits  $\mathsf{DuraLoc}^{\mathsf{TM}}$  tools.

61709-00-00 (US)

92682611 (Canada) 1 each

#### **TOOL HOLDERS**



## DuraLoc™ 24" Tool Holder System

Keep all your DuraLoc™ tools organized and off the floor with this unique snap-in storage system. Includes rail and 4 pucks with hardware.

61710-00-00 (US)

92682613 (Canada) 1 each



#### DuraLoc™ Tool Holder Double Hanger

Keep your DuraLoc™ tools organized and off the floor with this holder. Mounts directly to wall. Includes hardware.

61711-00-00 (US)

92682614 (Canada) 1 each



#### DuraLoc™ Tool Holder Single Hanger


Keep your DuraLoc™ tools organized and off the floor with this holder. Mounts directly to wall. Includes hardware.

61712-00-00 (US)

92682615 (Canada) 1 each



## Cleaning Caddy Products & Accessories



## Cleaning Caddy

Compact and easy to maneuver, similar footprint to mop and bucket. On-board tool storage. Rechargeable battery lasts four hours on a single charge. Easy-to-use control panel simplifies operation. Easy-access tank holds up to 13.5 gallons of water. Spray wand (90 PSI spray pressure) evenly distributes chemistry. Lock-and-key chemical dispensing. Wet vacuum removes dirty solution for a complete clean. 22" x 24"

Cleaning Caddy + Wet Vacuum 9265-1030 1 each Cleaning Caddy + Shelf 9265-1031 (US only) 1 each

#### **RESTROOM CLEANING & DISINFECTANTS**



#### Peroxide Multi Surface Cleaner & Disinfectant

One product to clean and disinfect all hard surfaces and glass for entire restroom and front of the house. EPA registered disinfectant with kill time as short as 3 minutes, killing norovirus as fast as 45 seconds.\*

EPA Reg. No. 1677-238, DIN 02412314

6100791 (US) 2-2 L 6100897 (Canada) 2-2 L

9215-0090 Conversion Kit

\*When diluted at 6 oz/gallon.



## 73 Disinfectant Acid Bathroom Cleaner

Heavy-duty bathroom cleaner ideal to remove hard water build-up and soap scum. EPA registered. Disinfects in 5 minutes with a pleasant fragrance.

EPA Reg. No. 1677-246

6101040 (US only) 2-2 L



#### 66 Heavy Duty Alkaline Bathroom Cleaner and Disinfectant

Heavy duty bathroom cleaner to remove soap scum or tough soils. EPA/DIN registered. Effective against norovirus.

EPA Reg. No. 1677-202, DIN 02274973

6110158 (US) 2-2 L 6120587 (Canada) 2-2 L 6114914 (US only) 1-2.5 gal

Learn more about reducing waste and controlling costs with proper **dilution** & **dispensing systems**.

p **39** 

**See Hand Hygiene** options for your restroom.

#### RESTROOM CLEANING & DISINFECTANTS CONTINUED





# Scrub Free Bathroom Cleaning & Disinfecting System

Full coverage foam, formulated for daily use to remove hard water build up and soap scum. Easily cleans and disinfects without the need for scrubbing.

6101797 1-2.5 gal 6101798 2-2 L



#### Oasis Pro<sup>™</sup> 16 Orange Force

Powerful, no-streak formula cleans greasy soils, film and smoke from multiple surfaces.

6121038 2-2 L



#### Glass Cleaner

Streak-free, fast-drying performance on windows, mirrors, glass, plastic, acrylics and painted surfaces. USDA Certified Bio-Based product.

6100289 2-2 L

#### **FLOOR CLEANERS**



#### MAXX Dual Action Floor Cleaner

Alkaline floor cleaner with fresh fragrance for daily cleaning and tackling greasy soils.

6100659 2-2 L

Control restroom odors with a variety of odor control solutions.

p **26** 



#### High Performance Neutral Cleaner

Daily, rinse-free, non-alkaline floor cleaner that delivers superior results with a fresh and clean fragrance.

6100035 2-2 L

#### REPLACEMENT PARTS

Wet Vacuum Filter Replacement

9265-2317 1 each

Wet Vacuum Head

9265-2997 1 each

Wet Vacuum Squeegee Blade Replacement Kit

9265-2322 (US only) 1 each

Dual-Surface Deck Brush - Blue

61803-01-00 (US only) 1 each

Fiberglass Interlocking Handle - Blue

61807-01-00 (US only) 1 each

"Disinfected Daily" Sticker - White

9265-2329 1 each

"Disinfected Daily" Sticker - Clear

9265-2328 1 each

Doorstop

9265-2327 1 each

Mop Sink Hose

9480-2188 1 each



## **Odor Control**



## **Bio-Enzymatic Odor Eliminator**

Eliminates odors at the source with continuous enzymatic action. Effective on hard and soft surfaces. Great for restroom and trash odors.

Waterfall mist scent.

6101024 1-2.5 gal 9.46 L



#### First Impression™ Simply Fragrance

Leaves restrooms smelling clean without aerosols. Mild scent.

Cucumber Melon	6101122	6-1.6 fl oz
Ocean Breeze	6102046	6-1.6 fl oz
Mandarin Burst	6102049	6-1.6 fl oz
Dispenser	9265-2192	1-4 pk





#### First Impression™ Micro Aerosol

Aerosol technology neutralizes malodors in hallways and restrooms. Programmable, automated dispensing.

Variety Pack	6101171	12-1.8 fl oz
Cucumber Melon/Starter Kit	6101121/6101172	12-1.8 fl oz
Mandarin Burst/Starter Kit	6130078/6130074	12-1.8 fl oz
Orchard Field/Starter Kit	6101120/6101173	12-1.8 fl oz
Summer Linen/Starter Kit	6130076/6130071	12-1.8 fl oz

## **Restroom Cleaners & Disinfectants**



# 73 Disinfectant Acid Bathroom Cleaner

Heavy duty bathroom cleaner ideal to remove hard water build-up and soap scum. EPA registered. Disinfects in 5 minutes with a pleasant fragrance.

EPA Reg. No. 1677-246

6101041 (US) 1-2.5 gal

Learn more about reducing waste and controlling costs with proper **dilution** & **dispensing systems**.

## Restroom Cleaners & Disinfectants CONTINUED





#### Peroxide Multi Surface Cleaner & Disinfectant

One product to clean and disinfect all hard surfaces and glass for entire restroom and front of the house. EPA/ DIN registered disinfectant with kill time as fast as 3 minutes. Notable claims include norovirus.

EPA Reg. No. 1677-238, DIN 02412314

6100693 (US) 1-2 gal 6100894 (Canada) 1-2.5 gal



#### 66 Heavy Duty Alkaline Bathroom Cleaner and Disinfectant

Heavy duty bathroom cleaner to remove soap scum or tough soils. EPA/DIN registered. Effective against norovirus.

EPA Reg. No. 1677-202, DIN 02274973

6110158 (US) 2-2 L 6120587 (Canada) 2-2 L 6114914 (US only) 1-2.5 gal



#### Glass Cleaner

Streak-free, fast-drying performance on windows, mirrors, glass, plastic, acrylics and painted surfaces. USDA Certified Bio-Based product.

6100288 1-2.5 gal



#### CBC Plus Bowl Cleaner

EPA registered, ready-to-use acidic restroom bowl cleaner.

EPA Reg. No 8155-7-42964

6105705 (Canada) 6-32 fl oz

**See floor cleaning** solutions to help keep restroom floors fresh.

p 20

## Tools & Accessories



#### AIM™ Urinal Screen Mango

Long-lasting fragrance and splash free design; releases optimized bacteria to consume malodors and inhibit deposit buildups with every flush.

6101859 10/case



## AIM™ Encounter Urinal Block with Screen

Each flush releases cleaning agents to inhibit deposit buildup and eliminate odors.

6144200 12-100 g



#### Public/Employee Restroom Start-Up Kit

Containment and disposal system for needles and sharps, designed specifically for restrooms.

50252-91-11 (US) 1 kit



#### Pump-Up Foamer/Sprayer

A 32-oz pump-up foamer and sprayer in one unit. Reduces repetitive motion injury by eliminating the need to pull a standard trigger sprayer.

9265-2603 (US)

9265-2602 (Canada) 1 each



## Nexa™

# A total hand hygiene solution

Help ensure your employees maintain proper hand hygiene with our full line of products backed up by training and service. Our efficient, innovative and sustainable system includes soaps, sanitizers and dispensers.



#### **GENERAL USE SOAPS & LOTION**



#### Nexa<sup>™</sup> Foam Hand Soap

Green Seal $^{\mathbb{N}}$  certified gentle foaming hand soap that is ideal for public restrooms.

6100708 6-750 mL 6100709 4-1250 mL



#### Nexa<sup>™</sup> Mild Foam Hand Soap

Green Seal<sup>™</sup> certified dye-free, fragrance-free gentle foam hand soap ideal for public restrooms.

6101194 (US only) 6-750 mL 6101193 (US only) 4-1250 mL



#### Nexa<sup>™</sup> Clean & Smooth

Green Seal™ certified lotion hand soap that provides rich lather to remove stubborn dirt while leaving hands fresh and soft.

6100706 6-750 mL 6100707 4-1250 mL



#### Nexa<sup>™</sup> Revitalizing Skin Lotion

Fragrance-free, advanced formula designed to be non-greasy and quick absorbing, providing great moisturization.

6000062 6-750 mL

#### ANTIBACTERIAL SOAPS



#### Nexa™ Advanced Antibacterial Foam Hand Soap

Pre-lathered foam soap with a light floral scent. This powerful but gentle formula is effective against bacteria that can cause illness while offering a pleasant experience for employees and guests.

6101090 (US only) 6-750 mL 6101088 (US only) 4-1250 mL



#### Nexa<sup>™</sup> Gentle Antibacterial Foam Hand Soap

Pre-lathered soap with a citrus scent and PCMX active. Effective against most common bacteria that may cause illness in food service environments.

6100719 (US only) 6-750 mL 6100720 (US only) 4-1250 mL



#### Nexa<sup>™</sup> Advanced Antibacterial Clean & Smooth

High-quality lotion soap with a light floral scent. Powerful but gentle formula is effective against bacteria that can cause illness while offering a pleasant experience for employees and guests.

6101421 6-750 mL 6101420 4-1250 mL



#### Nexa™ Antibacterial Clean & Smooth

High-quality lotion soap with a light floral scent. Powerful but gentle formula is effective against bacteria that can cause illness while offering a pleasant experience for employees and guests.

6100711 (Canada only) 6-750 mL 6100712 (Canada only) 4-1250 mL



#### Nexa<sup>™</sup> Digiclean Antibacterial Foam Hand Soap

Pre-lathered antibacterial soap with a light citrus scent that decreases bacteria on the skin.

6100754 (Canada only) 6-750 mL



#### Nexa<sup>™</sup> Digiclean E Foam Hand Soap

Antibacterial foam hand soap with citrus scent.

6100756 (Canada only) 6-750 mL

## Nexa<sup>™</sup> continued

#### **SANITIZERS**



#### Nexa<sup>™</sup> Foodservice Hand Sanitizer

FDA food code-compliant (non-alcohol based). Ideal for use in the kitchen or foodservice settings.

6100729 (US only) 6100730 (US only) 6-750 mL 4-1250 mL



#### Nexa<sup>™</sup> Instant Hand Sanitizer Gel

More than 99.5% effective in in-vitro testing against a range of foodborne illness-causing bacteria.

6100722 (US only) 6100723 (US only) 6-750 mL 4-1250 mL



#### Nexa<sup>™</sup> DigiSan E Foam Hand Sanitizer

FDA food code-compliant (non-alcohol based). Ideal for use in foodservice settings.

DIN 02242842

6100758 (Canada only) 6-750 mL 6100759 (Canada only) 4-1250 mL

See more products that can impact your employees' food safety compliance. p 32

#### **DISPENSERS**



#### Touch-Free Dispenser

Energy saving dispenser requires fewer battery change-outs. Patented pump reduces clogs and drips and helps to avoid costly product waste.

Nexa<sup>™</sup> Classic Touch-Free Dispenser

9202-1192 Black 1-1250 mL White 9202-1193 1-1250 mL

Nexa<sup>™</sup> Compact Touch-Free Dispenser

Black 9202-1190 1-750 mL White 9202-1191 1-750 mL



#### Manual Dispenser

Patented pump pulls excess product back in, reducing clogs and drips. Antimicrobial protection on the push bar continuously inhibits growth of bacteria, mold and mildew.

Nexa<sup>™</sup> Classic Manual Dispenser

9202-3091 Black 1-1250 mL 9202-3093 White 1-1250 mL

Nexa<sup>™</sup> Compact Manual Dispenser

Black 9202-3087 1-750 mL White 9202-3088 1-750 mL



#### Hand Sanitizer Stand

Hand Sanitizer Station (Includes White Nexa Classic Touch-Free Dispenser)

9202-6037 1 Unit





## Concentrates

#### ANTIBACTERIAL HAND SOAP



#### Concentrated Antibacterial Foam Hand Soap

Concentrated FDA-regulated foaming antibacterial soap with a benzalkonium chloride active and a light citrus scent. It can be diluted up to a 5:1 dilution rate.

6100867 2-2 L

#### **DISPENSERS**



Hand Care Concentrates Oasis™ Low Concentrate (Cosmetic & Sanitizer)

9202-1200 (US only) 1 unit

Hand Care Concentrates Oasis™ High Concentrate (AB)

9202-1201 (US only) 1 unit

#### **GENERAL USE HAND SOAP**



HAND SANITIZER

#### Concentrated Foam Hand Soap

Concentrated general use foam soap that can be diluted up to a 10:1 dilution rate.

Concentrated Foam Hand Sanitizer

2-2 L

FDA food code-compliant and alcohol free concentrated foam hand sanitizer with a benzalkonium chloride active. It can be diluted up to a 10:1 dilution rate.

6100740 2-2 L

#### **ACCESSORIES & TOOLS**



#### 1250 mL Refillable Bottle

9202-3330 4 pack 9202-3329 10 pack

#### 750 mL Refillable Bottle

9202-3328 4 pack 9202-3327 10 pack



#### Antibacterial Foam Hand Soap Bottle Label

9202-3318 (US only) 10/sheet



Foam Hand Soap Bottle Label

9202-3317 10/sheet



#### Foam Hand Sanitizer Bottle Label

9202-3319 (US only) 10/sheet

## Syncra<sup>™</sup> Soaps & Systems

6100868 (US only)

#### SOAPS



#### Syncra<sup>™</sup> Advanced Antibacterial Hand Soap

Pre-lathered foam soap with a light floral scent. This powerful but gentle formula is effective against bacteria that can cause illness while offering a pleasant experience for employees and guests.

6101087 (US only) 4-1200 mL



#### Syncra<sup>™</sup> Digiclean Antibacterial Foam Hand Soap

Pre-lathered antibacterial soap with a light citrus scent that decreases bacteria on the skin.

6100942 (Canada only) 4-1200 mL



#### Syncra<sup>™</sup> Foam Hand Soap

Green  $Seal^{\mathbb{M}}$  certified gentle foaming hand soap that is ideal for public restrooms.

6100865 4-1250 mL

## **Counter Mount**





#### Advanced Antibacterial Foam Hand Soap

Antibacterial foam hand soap moisturizes and reduces bacteria. Contains moisturizers.

(Counter mount dispenser) 6101086 (US only) 2-1600 mL



#### Foam Hand Soap

Green Seal™ certified gentle foaming cosmetic hand soap. Contains moisturizers.

(Counter mount dispenser)

6100122 2-1600 mL



#### **Counter Mount Touch-Free** Dispenser

Touch-free dispenser.

9263-1012 1 each



## **Bulk & RTU**



#### Advanced Antibacterial Clean & Smooth™

Antibacterial lotion soap that is gentle on hands and effective against germs.

6101419 (US only) 4-1 gal



#### Manual Bulk Dispenser

9263-1970 1 each



#### Antibacterial Clean & Smooth™

Antibacterial liquid hand soap moisturizes and reduces bacteria. Contains moisturizers.

6114886 (Canada only) 4-1 gal



#### Gel Hand Sanitizers

Waterless hand sanitizer with moisturizers to condition and helps reduce level of bacteria on hands.

6030352 (US) 144-1.2 fl oz 6000003 (US) 72-4 fl oz 12-540 mL 6000004 (US) 144-37 mL 6082125 (Canada) (moisturizing)

6000304 (Canada)

72-118 ml 6082540 (Canada) 12-540 mL



## Clean & Smooth™

Green Seal<sup>™</sup> certified gentle liquid hand soap.

4-1 gal 6115875



## Food Preparation & Rotation



# Antimicrobial Fruit & Vegetable Treatment

No-rinse treatment that reduces 99.9% of pathogens *E. coli, Listeria* and *Salmonella\** in wash water.

EPA Reg. No. 1677-234

6100283 (US) 1-2.5 gal 6100777 (Canada) 1-2.5 gal

\*E. coli 0157:H7, Listeria monocytogenes (or L. monocytogenes) and Salmonella enterica (or S. enterica) for raw agricultural commodities

#### Antimicrobial Fruit & Vegetable Treatment Test Strips



Test strips to be used with Ecolab Antimicrobial Fruit and Vegetable Treatment only.

EPA Reg. No. 1677-234

20314-01-11 (US) 100 strips 92332047 (Canada) 100 strips



#### Victory™

EPA registered antimicrobial wash additive that reduces microorganisms from the surface of fruits & vegetables, reducing spoilage and decay.

EPA Reg. No. 1677-186

6101962 1-58 oz 6115932 (US only) 2-58 oz



#### Peracetic Acid Test Strips

Test strips to be used with Victory<sup>™</sup> antimicrobial fruit and vegetable wash.

20313-01-11 (US) 50 strips 10041366 (Canada) 50 strips

## **Food Safety**



#### PREP-N-PRINT®

Print clear, legible, consistent labels every time. Automatic calculations keep you compliant, help overcome language barriers, increase labor productivity and reduce errors.

11900-04-00 1 unit



#### **Cutting Boards**

Reduce cross-contamination risks with color-coded cutting boards and knives. Anti-slip boards increase safety and reduce towel contamination. Six-Color Kits include: white, blue, yellow, red, brown and green. Also available individually. Anti-slip also available in purple for allergen control.

12" X 18" (30.5 X 45.5 cm)	30240-90-00	i set
15" x 20" (38 x 52 cm)	30241-90-00	1 set
18" x 24" (45.5 x 61 cm)	30242-90-00	1 set
Anti-slip (Shown above)		
13" x 19" (33 x 48 cm)	30250-90-00	1 set
16" x 21" (40.5 x 53.5 cm)	30251-90-00	1 set
19" x 25" (48 x 63.5 cm)	30252-90-00	1 set

## Visit foodsafety.ecolab.com for

food safety and food rotation products.

## **EcoSure® Solutions**



## EcoSure® CORE Food Safety Program

A single incident can compromise your customers, your employees and your reputation. Minimize food safety risk and drive behavior change with the EcoSure® Comprehensive Onsite Risk Evaluation (CORE) Food Safety Program.



#### **Onsite Expertise**

Our **comprehensive assessments** can expose risks and improve visibility into your operations. We conduct **coaching and training** to drive behavior changes and promote a culture of food safety. We also **recommend corrective actions and solutions** to minimize risks to your employees, guests, operations and brand.



#### Food Safety Support

Take advantage of a **variety of resources** that promote food safety like newsletters and webinars to **leverage the knowledge and expertise** of our food safety and public health experts. We also offer a hotline and **food safety readiness kits** for your staff, equipping them with prevention, response and other need-to-know information about common foodborne illnesses.

## EcoSure® Norovirus Control Program

Ecolab can help you drive behavior change and minimize risk against foodborne illness.

# OUTBREAK PREVENTION

# INCIDENT RESPONSE

#### **Education & Training**

We help educate your managers on the risks and causes surrounding norovirus and train them in prevention and response. We support you in establishing a norovirus "champion" who works to promote a culture of prevention and helps train employees.

#### **Prevention and Response Tools**

EcoSure® is designed to equip your employees with essential information, practical and easy-to-use tools and step-by-step instructions to prevent and respond to norovirus events.



## **Water Systems**

# Water Program from Ecolab Expert service and peace of mind

Our water program is customized to fit your unique needs. We offer on-site water quality testing, technical water analysis and regular maintenance programs, all backed by our world-class service.

#### **PROBLEM**

- CHLORINE/CHLORAMINES Produces an off taste and corrodes equipment
- SEDIMENT
  Clouds beverages, damages equipment
- MICROORGANISMS
  Leads to illness
- TOTAL DISSOLVED SOLIDS (TDS)
  Causes equipment downtime
- NATER MINERALS Leads to equipment downtime

#### **SOLUTION**

- CARBON FILTRATION
- PHYSICAL FILTRATION
- ADVANCED PHYSICAL FILTRATION

#### PRE-FILTRATION SYSTEMS







#### Single Head with Pressure Gauge

Can be added retroactively to existing High Capacity filtration systems.

9320-2425 (US only) 1 each

## Twin Head with Pressure Gauge

Use when installing new high capacity filtration systems in heavy sediment areas.

9320-2426 (US only) 1 each

#### Upgrade Kit

Upgrade Kit can be added to existing single High Capacity manifold to convert to Twin Series.

9320-2424 (US only) 1 each

#### **FILTER SYSTEMS**









#### High Capacity Single System

Single head filtration system for use with high capacity filters.

9320-2266 1 each

## High Capacity Twin System

Double head filtration system for increased capacity and flow rate on large applications.

9320-2267 1 each

#### High Capacity Split Twin System

One inlet with two outlets to simultaneously treat two different applications, such as ice and post mix.

9320-2268 1 each

#### **ECO-SLF System**

Single head system for use with the ECO-350 and ECO-350S filters.

9320-2270 1 each



#### Replacement Cartridges

Other legacy Ecolab and common competitive filter replacements are also available. Contact your Ecolab representative for more information.

#### Filters

#### **FILTER CARTRIDGES**



## High Capacity Filter Cartridge

Patented hollow carbon technology removes chlorine, chloramine and ultra-fine particles to improve beverage taste, odor and carbonation.

10" 50,000 gal Cartridge 9320-2198 1 each

14" 75,000 gal Cartridge

9320-2207 1 each

20" 100,000 gal Cartridge

9320-2250 1 each



#### ECO-350

Hollow carbon technology in a slim, compact design for improved water quality on smaller applications (up to 1.7 gpm) and in tight spaces.

10" 20,000 gal Cartridge 9320-2350 1 each STOLAR PART STATE TO

#### ECO-315T05

Capsule design provides even greater flexibility in positioning to improve beverage quality in the tightest spaces. Starter kit needed for install.

16.1" 6,000 gal Cartridge 9320-1035 (starter kit) 9320-1037

1 each 1 each

#### **SCALE CONTROL FILTERS**



#### High Capacity Scale Control Filter Cartridge

Patented hollow carbon technology removes chlorine, chloramines, and ultra-fine particles. Improves ice and brewed beverage quality and helps protect equipment from sediment and scale.

10" 50,000 gal Cartridge

9320-2256 1 each

14" 75,000 gal Cartridge

9320-2258 1 each

20" 100,000 gal Cartridge

9320-2259 1 each



#### ECO-350 Filter Cartridge

Hollow carbon technology in a slim, compact design, great for standard brewers and ice machines up to 600 lbs.

10" 20,000 gal Cartridge 9320-2351

1 each



#### Capsule TODS Filter

Capsule design provides even greater flexibility in positioning to protect small ice machines and brewers in the tightest spaces. Starter kit needed for install.

16.1" 6,000 gal Cartridge 9320-1035 (starter kit) 9320-1042

1 each 1 each

#### SPECIALTY FILTERS



#### High Capacity SED10S+

Non carbon-based media helps to protect ice machines from scale and sediment. Ideal solution for those seeking compliance with ASHRAE Standard 188.

10" 75,000 gal Cartridge.

9320-2363 (US only) 1 each



#### High Capacity Ion Exchange Filter

Ion exchange resin reduces total dissolved solids and water hardness. Great for coffee, tea, espresso, steamers and combi-ovens.

14" 9,000 grain Cartridge 9320-2261

20" 15,000 grain Cartridge 9320-2262

1 each 1 each



#### ECO-SED20 High Capacity Pre-filter

Dual Stage Filtration Technology reduces fine and coarse particulates and protects carbon filter. Ideal solution for heavy sediment water areas.

93202390 (US only)

1 each



## Parts & Install Kits



#### Braided Hose Install Kit

Includes tubing, fittings, barbs, clamps, and wall anchors.

1/2" Hose 9320-1094 1 each 1/8" Hose 9320-1095 1 each 1/8" hose 9320-1095 1 each 1/8" hose 9320-1095 1 each 1/8" hose 9320-1095



#### Bypass Plug

Use to bypass any High Capacity filtration systems.

9320-2272 1 each



#### Capsule Starter Kit

Mounting bracket for initial install of capsule filter.

9320-1035 1 each

#### **Hot Water Filtration**



#### Hot Water Filtration Products

Stainless steel construction meant for laundry or warewashing, appropriate for temperatures under 275° F. Order cartridges separately.

Max flow rate 10, 250 psi dynamic pressure	9320-3248	1 each
Replacement cartridge	9320-1023	1 cartridge
Max flow rate 15, 250 psi dynamic pressure	9320-3255	1 each
Replacement cartridge	9320-1024	1 cartridge
Max flow rate 28, 125 psi dynamic pressure	9320-3263 (US only)	1 each
Replacement cartridge	9320-1023 (US only)	1 cartridge
Max flow rate 56, 125 psi dynamic pressure	9320-3271 (US only)	1 each
Replacement cartridge	9320-1024 (US only)	1 cartridge

## **Water Softeners**





p 21

#### Point of Use Softener

Twin tank point of use softener provides uninterrupted soft water with proven reliability at temperatures up to 150° F and integrated backflow prevention. Compact design fits under standard dish tables.

HTSS-150 for door and most conveyor machines 9320-2237 1 each

HWS-FLT for conveyors >66" and flight machines 9320-2170 1 each

## See specialty cleaning products

that can also impact Beverage Quality.



#### Point of Entry Softener

Twin tank non-electric design with metered regeneration provides uninterrupted flow of soft water to the kitchen while optimizing salt and water use.

CP-150 two 10" x 54" tanks 9320-2148 (US only) 1 each CP-250 two 13" x 54" tanks 9320-2149 (US only) 1 each





# Designed specifically for foodservice operations

Contains quality Ecolab **first-aid products and tools** used to support accidents and injuries that occur in the kitchen environment, including burns, cuts, eye injuries, and strains/sprains.



#### Ecolab CarePod™ Essentials First Aid Kit

The main cabinet complete with all products.

50225-90-11 1 each



#### Ecolab CarePod™ Premium First Aid Kit

The main cabinet with all products plus the empty storage cabinet.

50225-91-11 1 each



#### Ecolab CarePod™ Essentials First Aid Kit with Biohazard

The main cabinet with product plus the biohazard cabinet with product.

50225-93-11 1 each



#### Ecolab CarePod™ Premium First Aid Kit with Biohazard

The main cabinet with product plus the empty storage cabinet plus the biohazard cabinet with product.

50225-92-11 1 each



#### Ecolab CarePod™ First Aid Storage Cabinet

The empty storage cabinet. 50225-11-11 1 each



#### Ecolab CarePod™ Biohazard Spill Kit

The biohazard cabinet with product.

50226-90-11 1 each

## PPE & Spill Kits



## Personal Protective Equipment (PPE) Kit

Keep employees safe with an apron, goggles and elbow-length gloves for greasy cleaning.

50604-92-31 (US) 10042002 (Canada) 1 kit



#### Biohazard Response Spill Kit

Cleans and disinfects non-food spills/ accidents. Refill kit available. Includes EPA registered product.

1 kit

50258-91-11 (US only) 1 kit

Kit refill with chemical

50258-01-11 (US only) 1 kit



#### Canada Biohazard Response Kit

Cleans and disinfects non-food spills/accidents. Order one each of the four items for a complete kit.

Biohazard Response Kit Case

10041915 (Canada only) case only

Biohazard Response Kit Refill 2-Pack without chemical

10041916 (Canada only) 1 kit

Spray Bottle Holder

92022617 (Canada only) 1 holder

Asepticare Disinfectant Aerosol DIN Registered product. DIN: 00801828 61116002 (Canada only) 12-397 g



## Warewashing



## SMARTPOWER™ Controller and IO Box Installation Kit

Includes installation parts for a SMARTPOWER™ warewashing system.

2-Product Kit 9233-1120 1 unit 3-Product Kit 9233-1119 1 unit



## SMARTPOWER<sup>™</sup> Machine Detergent Dispenser

Dispenser for SMARTPOWER  $^{\!\scriptscriptstyle{\mathrm{TM}}}$  machine warewashing detergent.

9223-1124 1 each



#### SMARTPOWER™ Sanitizer Dispenser RTU

Dispenser for SMARTPOWER<sup>™</sup> for 3 compartment sink. 9223-1159 1 each



#### SMARTPOWER™ Rinse Aid Dispenser

Dispenser for SMARTPOWER  $^{\!\scriptscriptstyle{\mathrm{TM}}}$  machine warewashing rinse additive.

9223-1125 1 each



# SMARTPOWER™ Detergent Manual Dispenser RTU

Dispenser for SMARTPOWER™ manual detergent for 3 compartment sink.

9223-1160 1 each

**SMARTPOWER**<sup>™</sup> **blocks** are shapeand color-coded for easy dispensing. Learn more about SMARTPOWER<sup>™</sup> products.

## Warewashing CONTINUED





# SMARTPOWER™ Presoak for Cutlery/Flatware Dispenser RTU

Dispenser for SMARTPOWER™ Presoak for flatware.

9223-1161 1 each

#### Apex™ to SMARTPOWER™ Manual Detergent Dispenser Conversion Kit

Contains pentagon product guide with o-ring, pentagon product ID and o-ring grease.

9223-2536 1 each



#### SMARTPOWER™ Hydraulic Pot and Pan Presoak Dispenser

Dispenser for  $SMARTPOWER^{TM}$  Presoak for pots and pans.

9223-1132 1 each

#### Apex™ to SMARTPOWER™ Flatware Presoak Dispenser Conversion Kit

Contains square product guide with o-ring, pentagon product ID and o-ring grease.

9223-2538 1 each



#### SMARTPOWER™ Pot and Pan Presoak Electromatic

Dispenser for SMARTPOWER $^{\text{\tiny{M}}}$  Presoak for pots and pans.

9223-1129 1 each

#### Apex™ to SMARTPOWER™ Hydraulic Pot and Pan Presoak Dispenser Conversion Kit

Contains square product guide with o-ring, pentagon product ID and o-ring grease.

9223-1126 1 each

#### Wash Max Dispenser

Dispenser for solid detergents.

9237-1103

#### Rinse Max II Dispenser

Dispenser for solid rinse.

9218-1494

#### Geocenter with Cell Packed

Dispenser for solid warewash machine detergent.

9223-1091

## **Concentrates**

#### Oasis Pro<sup>™</sup> Select 4 Dispenser

For any Oasis 2.5 gal container products. Accommodates 4 products.

9215-1149 Spray Bottle 9215-1150 Mop Bucket

#### Oasis Pro<sup>™</sup> Ultra 1 System

For any Oasis 2.5 gal container products. Accommodates 1 product.

9215-1151 Spray Bottle 9215-1152 Mop Bucket

#### Oasis Pro<sup>™</sup> 2-2L Product Holder

Box compartment for single 2-2 L bag products.

9215-1154



SMART**POWER**™

## It's time to shine.

Partner with Ecolab to solve your toughest warewashing challenges with the complete program, combining powerful chemistry with smart technology and personalized service.





Visit www.ecolab.com/smartpower or call 1.800.35.CLEAN to learn more about SMARTPOWER.™

